




RIV 230

Soupape de suppression à ressort avec écoulement libre

>> Dessin techniques et tableaux



DN	Codice	Ø	H	L	PN	KG	P/box
1"	050230000007	25	152	61	1,5bar - 21psi	0,454	20
1"1/2	050230000009	39	156	66	1,5bar - 21psi	0,760	15
2"	050230000011	51	160	77	1,5bar - 21psi	1,095	10

>> Avantages


Réalisée pour garantir le respect maximal de l'environnement; en effet, elle est dotée d'un raccord porte-caoutchouc sur lequel il est possible d'appliquer un tuyau pour évacuer d'éventuels purgeurs d'air dans un réservoir spécial.

La soupape peut être facilement réglée en fonction de la pression désirée (de 0,5 à 1,5 bar - de 7 à 21 Psi) et peut être scellée en mode inviolable à l'aide des ailettes perforées.

Certifiée conformément à la Directive 97/23/CE (PED), le matériel marqué **CE 1115**.

>> Données techniques

RIV 250




Branchement ISO 228/1, ANSI B1.20.1 (NPT)

Limites -20°C (-4°F) (sans liquide) +180°C (+356°F)

Notes La pression max. de utilisation (PN) s'entend avec une température ambiante de environ 23°C.

>> Riv 230 RIV 250 RIV 251 – PRESSURE RELIEF VALVES - SETTING INSTRUCTION



>> Picture 1

- 1) Unscrew the lock nut "A"
 - 2) Turn the spring-tightener "B"
- Clockwise to increase the pressure
Anti-clockwise to reduce the pressure

>> Picture 2

Once obtained the desired pressure, screw down the lock nut "A"

>> Picture 3

Fix the setting, using the rings "C"

Situated on the body and on the spring-tightener